

RG 8/U Type

Coaxial Cable



PRODUCT CONSTRUCTION:

Conductors: Copper per ASTM B3

Insulation/Core: Solid and foam polyethylene

Shield: Tinned or bare copper braid · Flexfoil® shield

Jacket: Premium PVC compound

Applications: Suitable for RF signal transmission · Broadcast

Packaging: Please contact Customer Service for packaging and color options

APPLICATION PROPERTIES

Flame retardant	No	Resistant to UV	No
Halogen free	No	Outdoor installation	No
Low smoke	No	Underground installation	No
Oil resistant	No		

STANDARDS AND APPROVALS



ELECTRICAL PROPERTIES

Catalog Number	AWG / Kcmil	Nom. insulation o.d. [in]	Nominal diameter over insulation [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
C1198	11	0.285	7.2	0.405	10.29
C1154	13	0.285	7.2	0.405	10.29

We reserve the right to do changes as a result of running product development and/or changes in standards