

XC RG58

RG coax cable for video use



PRODUCT CONSTRUCTION:

Conductors: Copper per ASTM B3 · Tinned copper per ASTM B33

Insulation/Core: Solid and foam polyethylene (PE) · Foam fluoropolymer (FEP)

Shield: Tinned copper braid

Jacket: Premium PVC compound

Applications: Suitable for RF signal transmission · Broadcast · LAN & data transmission

APPLICATION PROPERTIES

Flame retardant	No	Outdoor installation	No
Halogen free	No	Underground installation	No
Resistant to UV	No		

STANDARDS AND APPROVALS



ELECTRICAL PROPERTIES

Catalog Number	AWG / Kcmil	Nom. insulation o.d. [in]	Nominal diameter over insulation [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
C1155	20	0.116	2.9	0.195	4.95
C3519	19	0.102	2.6	0.157	3.99
C1178A	20	0.116	2.9	0.195	4.95
C1188	20	0.114	2.9	0.2	4.95

We reserve the right to do changes as a result of running product development and/or changes in standards