

# N2XS(FL)2Y 6/10KV 1X300RM/25 CPR F



Cross-section (mm <sup>2</sup> )	Direct in ground trefoil (A)	Direct in ground flat spaced (A)	Air trefoil (A)	Air flat spaced (A)
70	268	302	294	350
95	320	359	358	426
120	363	405	413	491
150	405	442	468	549
185	456	493	535	625
240	526	563	631	731
300	591	626	722	831
400	662	675	827	920
500	744	748	949	1043
630	830	811	1082	1158
800	910	870	1215	1265
1000	980	917	1331	1350