

FP100®

Fire Resistant Single Core Cable. 450/750 V



Prysmian FP100 is the original fire resistant low voltage single core cable for use in steel conduits

KEY APPLICATIONS

FP100® is ideally suited to drawing into conduit installations that provide adequate mechanical protection and it forms the key part of a wiring system for evacuation and fire fighting applications.

Green/Yellow is also suitable as a separate earth.

FEATURES AND BENEFITS

- Ideal for rewiring existing steel conduit and upgrade to a fire resistant system or where the added mechanical protection or utilisation of a steel conduit is required
- Tough robust insulation prevents damage during installation
- Low smoke and corrosive gas emissions Low Smoke, Zero Halogen (LSOH®)
- Manufactured under ISO 9001 Quality management systems

ADDITIONAL TECHNICAL SUPPORT

- [FAQ's](https://uk.prysmian.com/technical-area/faqs) - uk.prysmian.com/technical-area/faqs
- [Technical email](mailto:tech.info@prysmian.com) - tech.info@prysmian.com
- [Live Chat](https://uk.prysmian.com/technical-area) - uk.prysmian.com/technical-area
- Technical hotline: 02380 295222

STANDARDS



BS 6387 Category CWZ

IEC 60331-21

BS EN 60332-1-2

BS EN 61034-2

BS EN 60754-1

Fire Resistant Tests

Fire Resistant Test

Flame Propagation - Single Cable

Smoke emission

Corrosive and acid gas

CONSTRUCTION

Conductor material

Conductor surface

Core insulation material

Copper

Bare

Mica + polymer

APPLICATIONS PROPERTIES

Nominal voltage U ₀ [V]	450
Nominal voltage U [V]	750
Flame retardant	In accordance with BS EN 60332-1-2
Halogen free	Yes
Low smoke	Yes
Max. conductor temperature [°C]	90
Min. Operation temperature [°C]	-25
Min. Installation temperature [°C]	0
Max. Installation temperature [°C]	80
Bending radius (rule)	6D

COLOURS

A range of insulation colours are available, including green/yellow

CURRENT RATINGS

Refer to table 4E1 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations

Note: Where a conductor operates at a temperature exceeding 70°C it shall be ascertained that the equipment connected to the conductor is suitable for the conductor operating temperature

TECHNICAL DATA

Nominal cross section conductor [mm²]	Conductor category	Nominal thickness insulation [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO2e kg/km]
95	Class 2 = stranded	1.6	16	965	0.193	2,640
120	Class 2 = stranded	1.6	17.4	1,200	0.153	3,210
150	Class 2 = stranded	1.8	19.3	1,500	0.124	3,929
185	Class 2 = stranded	2	22	1,850	0.0991	4,886
240	Class 2 = stranded	2.2	25	2,400	0.0754	6,266
300	Class 2 = stranded	2.4	27	3,100	0.0601	7,920
400	Class 2 = stranded	2.6	31	3,800	0.047	9,947
500	Class 2 = stranded	2.8	35	4,900	0.0366	12,694
630	Class 2 = stranded	2.8	38	6,200	0.0283	16,236

*The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here: <https://uk.prysmiangroup.com/embodied-carbon>