

## 6241Y

**PVC Flat Wiring Cable with Bare CPC. BS 6004. 300/500 V**



Prysmian 6241Y is a flat PVC insulated and sheathed low voltage wiring cable typically used for small power and lighting applications

Single core with bare CPC

### KEY APPLICATIONS

Suitable for fixed installation in industrial, commercial and domestic premises, installation in walls, on boards, in conduit, trunking or embedded in plaster for small power and lighting applications

### FEATURES AND BENEFITS

- Ideal for lighting and switching circuits
- Easy to strip
- Manufactured under ISO 9001 Quality management systems

### ADDITIONAL TECHNICAL SUPPORT

- [FAQ's](https://uk.prysmian.com/technical-area/faqs) - [uk.prysmian.com/technical-area/faqs](https://uk.prysmian.com/technical-area/faqs)
- [Technical email](mailto:tech.info@prysmian.com) - [tech.info@prysmian.com](mailto:tech.info@prysmian.com)
- [Live Chat](https://uk.prysmian.com/technical-area) - [uk.prysmian.com/technical-area](https://uk.prysmian.com/technical-area)
- Technical hotline: 02380 295222

### STANDARDS



**BS 6004**

**BS EN 60332-1-2**

Construction Standard

Flame Propagation - Single Cable

### CONSTRUCTION

Conductor material  
Conductor surface  
Core insulation material  
Material outer sheath  
Cable shape

Copper  
Bare  
Polyvinyl chloride (PVC)  
Polyvinyl chloride (PVC)  
Flat

## APPLICATIONS PROPERTIES

Nominal voltage U <sub>0</sub> [V]	300
Nominal voltage U [V]	500
Flame retardant	In accordance with BS EN 60332-1-2
Max. conductor temperature [°C]	70
Min. Operation temperature [°C]	-15
Min. Installation temperature [°C]	0
Max. Installation temperature [°C]	60
Bending radius (rule)	4D (Minor axis)

## COLOURS

Insulation: Brown or Blue  
Sheath: Grey

## CURRENT RATINGS

Refer to table 4D5 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations

## TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm <sup>2</sup> ]	Conductor category	Nominal cross section of protective conductor [mm <sup>2</sup> ]	Cable height approx. [mm]	Cable width approx. [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO <sub>2</sub> e kg/km]
1	1	Class 1 = solid	1	4.5	5.6	38	18.1	100
1	1.5	Class 1 = solid	1	4.7	5.8	46	12.1	119

\*The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here: <https://uk.prysmiangroup.com/embodied-carbon>