

# **FP400**®

Fire Resistant Armoured Power Cable. BS 7846-F2. 600/1000 V





Prysmian FP400 is a tough, armoured cable with low fire hazard properties and limited fire resistance

#### **KEY APPLICATIONS**

Designed primarily for clipped directly to a surface, on tray, in basket or in free air. Fire resistant, low fire hazard armoured power and control cable that can also be laid direct in ground or in ducts in free draining soil, or embedded in concrete.

Use for fire performance circuits in public buildings.

#### **FEATURES AND BENEFITS**

- Fire resistant to BS 7846 F2
- Robust armour provides cable with added mechanical protection
- Reduced flame propagation
- Low smoke and corrosive gas emissions Low Smoke, Zero Halogen (LSOH®)
- Manufactured under ISO 9001 Quality management systems
- Designed to meet the requirements of London Underground LUL S1085 Fire Safety Performance of Materials Stations and Tunnel Infrastructure
- Multi core steel wire armour

## **ADDITIONAL TECHNICAL SUPPORT**

- FAQ's- uk.prysmian.com/technical-area/faqs
- <u>Technical email</u> tech.info@prysmian.com
- <u>Live Chat</u> uk.prysmian.com/technical-area
- Technical hotline: 02380 295222

#### **STANDARDS**





BS 7846 - Category F2 BS 6387 Category CWZ BS EN 61034-2 BS EN 60754-1 BS EN 60332-1-2 BS EN 60332-3-24 Construction Standard
Fire Resistant Tests
Smoke emission
Corrosive and acid gas
Flame Propagation - Single Cable
Flame Propagation - Multiple (bunched) Cables - Category C



## CONSTRUCTION

Conductor material Copper Conductor surface Bare Core insulation material

Mica + XLPE

Armouring/reinforcement Wire Armouring Yes

Material inner sheath Low smoke zero halogen Material outer sheath Low smoke zero halogen

Cable shape Round

#### **APPLICATIONS PROPERTIES**

600 Nominal voltage U0 [V] 1,000 Nominal voltage U [V]

Flame retardant In accordance with BS EN 60332-3-24

Halogen free Yes Yes Low smoke 90 Max. conductor temperature [°C] Min. Operation temperature [°C] -25 **UV** resistant Yes Outdoor installation Yes Min. Installation temperature [°C] 0 Max. Installation temperature [°C] 80 Underground installation Yes Bending radius (rule) 8D

## **COLOURS**

Insulation: Two Cores: Brown, Blue; Three Cores: Brown, Black, Grey; Four Cores: Blue, Brown, Black, Grey;

Five Cores: Blue, Brown, Black, Grey, Green/Yellow;

7 to 37 Cores: White (with printed numbers);

Sheath:Black

## **CURRENT RATINGS**

Refer to table 4E4 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations

Note: Where a conductor operates at a temperature exceeding 70°C it shall be ascertained that the equipment connected to the conductor is suitable for the conductor operating temperature



# **TECHNICAL DATA**

Number of cores	Nominal cross section conductor [mm²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO2e kg/km]
2	1.5	Round	0.9	9.1	13.4	345	12.1	1,017
2	2.5	Round	0.9	10.2	14.8	415	7.41	1,134
2	4	Round	0.9	11.4	15.8	480	4.61	1,271
2	6	Round	0.9	12	16.6	550	3.08	1,441
2	10	Round	0.9	15.1	19.8	740	1.83	2,188
2	25	Round	1.25	19.6	26	1,400	0.727	3,242
2	35	Round	1.6	23	29	1,900	0.524	4,503
2	70	Sector- shaped	1.6	25	33	2,600	0.268	6,139
2	120	Sector- shaped	2	29	37	3,900	0.153	9,973
3	1.5	Round	0.9	9.3	13.9	370	12.1	1,184
3	2.5	Round	0.9	10.8	15.4	455	7.41	1,352
3	4	Round	0.9	11.6	16.3	525	4.61	1,505
3	6	Round	0.9	13.3	17.8	650	3.08	1,796
3	10	Round	1.25	16	22	1,000	1.83	2,968
3	16	Round	1.25	17.6	24	1,250	1.15	3,207
3	35	Round	1.6	25	32	2,300	0.524	5,654
3	70	Sector- shaped	1.6	28	35	3,300	0.268	8,128
4	1.5	Round	0.9	10.2	14.8	415	12.1	1,397
4	2.5	Round	0.9	12.1	16.9	530	7.41	1,623
4	4	Round	0.9	13	17.6	610	4.61	1,796
4	6	Round	1.25	14.7	21	880	3.08	2,400
4	10	Round	1.25	17.6	24	1,150	1.83	3,544
4	16	Round	1.25	19.3	25	1,450	1.15	3,861
4	25	Round	1.6	24	30	2,200	0.727	5,268
4	35	Round	1.6	28	34	2,800	0.524	6,995



# **TECHNICAL DATA**

Number of cores	Nominal cross section conductor [mm²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO2e kg/km]
4	50	Sector- shaped	1.6	29	35	3,200	0.387	7,840
4	70	Sector- shaped	2	31	39	4,200	0.268	11,514
4	95	Sector- shaped	2	34	42	5,300	0.193	13,889
4	120	Sector- shaped	2.5	38	48	6,800	0.153	17,559
4	150	Sector- shaped	2.5	42	52	8,100	0.124	20,749
4	185	Sector- shaped	2.5	47	57	9,900	0.0991	25,285
4	240	Sector- shaped	2.5	53	63	12,200	0.0754	31,287
4	300	Sector- shaped	2.5	58	68	14,900	0.0601	38,237
4	400	Sector- shaped	3.15	65	77	19,400	0.047	48,930
5	1.5	Round	0.9	11.2	15.6	445	12.1	1,585
5	2.5	Round	0.9	12.9	17.3	550	7.41	1,805
5	4	Round	0.9	14.2	18.7	660	4.61	2,050
5	6	Round	1.25	16.3	23	990	3.08	2,796
7	1.5	Round	0.9	12.2	16.8	520	12.1	2,134
7	2.5	Round	0.9	14.9	19.4	700	7.41	2,453
12	1.5	Round	1.25	16.2	22	860	12.1	3,490
19	1.5	Round	1.25	19	25	1,150	12.1	4,893
27	1.5	Round	1.6	24	30	1,650	12.1	7,011
37	1.5	Round	1.6	27	33	1,950	12.1	8,991

<sup>\*</sup>The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here: <a href="https://uk.prysmiangroup.com/embodied-carbon">https://uk.prysmiangroup.com/embodied-carbon</a>