
6242Y

PVC Flat Wiring Cable with Bare CPC. BS 6004. 300/500 V



Prysmian 6242Y is a flat PVC insulated and sheathed low voltage wiring cable typically used for small power and lighting applications. Two cores with bare CPC

KEY APPLICATIONS

Suitable for fixed installation in industrial, commercial and domestic premises, installation in walls, on boards, in conduit, trunking or embedded in plaster for small power and lighting applications

FEATURES AND BENEFITS

- Ideal for ring and radial circuits
- Ideal for lighting and switching circuits
- Easy to strip
- Manufactured under ISO 9001 Quality management systems

ADDITIONAL TECHNICAL SUPPORT

- FAQ's- uk.prysmian.com/technical-area/faqs
- Technical email - tech.info@prysmian.com
- Live Chat - uk.prysmian.com/technical-area
- Technical hotline: 02380 295222

STANDARDS

BS 6004	Construction Standard
BS EN 60332-1-2	Flame Propagation - Single Cable

CONSTRUCTION

Conductor material	Copper
Conductor surface	Bare
Core insulation material	Polyvinyl chloride (PVC)
Material outer sheath	Polyvinyl chloride (PVC)
Cable shape	Flat

APPLICATIONS PROPERTIES

Nominal voltage U0 [V]	300
Nominal voltage U [V]	500
Flame retardant	In accordance with BS EN 60332-1-2
Max. conductor temperature [°C]	70
Min. Operation temperature [°C]	-15
Min. Installation temperature [°C]	0
Max. Installation temperature [°C]	60
Bending radius (rule)	4D (Minor axis)

COLOURS

Insulation: Brown, Blue

Alternatively, Brown, Brown (for 2x1.0 and 2x1.5 only)

Sheath: Grey

CURRENT RATINGS

Refer to table 4D5 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations

SUSTAINABILITY COMMITMENT

At Prysmian, sustainability is at the heart of our mission. By using sustainable processes and materials we are at the forefront of green innovation , promoting resource efficiency in our operations. We also partner with other sustainable companies to advocate responsible practices across our supply chain to reflect our commitment to a greener future. Discover how we are driving the future of sustainable cable and system solutions: Sustainability in the UK | Prysmian.

Scan to find out more

Copyright Prysmian, all rights reserved. You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this document without written consent of Prysmian. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian. Any modification or alteration of products may cause different results. Prysmian reserves the right to amend the information within this document at any time without notice. For the most up to date information, please contact us. You agree that, in placing any order, you have not relied on the information set out in this document. Prysmian disclaims any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product to the maximum extent permissible by law.

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm²]	Conductor category	Nominal cross section of protective conductor [mm²]	Cable height approx. [mm]	Cable width approx. [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO2e kg/km]
2	1	Class 1 = solid	1	4.5	8.2	58	18.1	149
2	1.5	Class 1 = solid	1	4.7	8.6	74	12.1	185
2	2.5	Class 1 = solid	1.5	5.3	9.9	110	7.41	269
2	4	Class 2 = stranded	1.5	6.1	11.4	155	4.61	404
2	6	Class 2 = stranded	2.5	6.8	13.1	215	3.08	563
2	10	Class 2 = stranded	4	8.4	16.8	350	1.83	948
2	16	Class 2 = stranded	6	9.6	19.5	520	1.15	1,348

*The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here:https://uk.prysmiangroup.com/embodied-carbon