

BS 5467 1kV

PVC Copper Conductor Armoured Cable. BS 5467. 600/1000 V



Prysmian BS 5467 is a low voltage armoured cable for industrial wiring and mains distribution

KEY APPLICATIONS

Designed primarily for clipped directly to a surface, on tray, in basket or in free air. These cables can also be laid direct in ground or in ducts in free draining soil, or embedded in concrete

The design of Prysmian BS 5467 is particularly robust and is well suited to areas at risk of mechanical damage.

FEATURES AND BENEFITS

- Manufactured under ISO 9001 Quality management systems
- Single core aluminium wire armour
- Multi core steel wire armour

ADDITIONAL TECHNICAL SUPPORT

- [FAQ's](https://uk.prysmian.com/technical-area/faqs) - uk.prysmian.com/technical-area/faqs
- [Technical email](mailto:tech.info@prysmian.com) - tech.info@prysmian.com
- [Live Chat](https://uk.prysmian.com/technical-area) - uk.prysmian.com/technical-area
- Technical hotline: 02380 295222

STANDARDS



BS 5467
BS EN 60332-1-2

Construction Standard
Flame Propagation - Single Cable

CONSTRUCTION

Conductor material	Copper
Conductor surface	Bare
Core insulation material	XLPE
Armouring/reinforcement	Wire
Armouring	Yes
Material inner sheath	Polyvinyl chloride (PVC)
Material outer sheath	Polyvinyl chloride (PVC)
Cable shape	Round

APPLICATIONS PROPERTIES

Nominal voltage U ₀ [V]	600
Nominal voltage U [V]	1,000
Flame retardant	In accordance with BS EN 60332-1-2
Max. conductor temperature [°C]	90
Min. Operation temperature [°C]	-15
UV resistant	Yes
Outdoor installation	Yes
Min. Installation temperature [°C]	0
Max. Installation temperature [°C]	80
Underground installation	Yes
Bending radius (rule)	8D

COLOURS

Insulation: Single Core: Brown or Blue;
 Two Cores: Brown, Blue;
 Three Cores: Brown, Black, Grey;
 Four Cores: Blue, Brown, Black, Grey;
 Five Cores: Blue, Brown, Black, Grey, Green/Yellow;
 7 to 37 Cores: White (with printed numbers);
 Sheath: Black

CURRENT RATINGS

Refer to table 4E3 and 4E4 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations
 Note: Where conductor operates at a temperature exceeding 70°C it shall be ascertained that the equipment connected to the conductor is suitable for the conductor operating temperature.

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm ²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO ₂ e kg/km]
1	150	Round	1.6	23	27	1,850	0.124	6,930
1	185	Round	1.6	25	29	2,300	0.0991	7,531
1	240	Round	1.6	27	31	2,900	0.0754	9,741
1	300	Round	1.6	30	34	3,500	0.0601	11,428
1	400	Round	2	35	39	4,500	0.047	14,022
1	500	Round	2	38	43	5,600	0.0366	17,918
1	630	Round	2	42	46	7,000	0.0283	21,940
1	800	Round	2.5	49	54	9,000	0.0221	29,255
1	1,000	Round	2.5	54	59	11,400	0.0176	83,936
2	1.5	Round	0.9	8.7	11.3	260	12.1	670
2	2.5	Round	0.9	9.9	12.7	330	7.41	805
2	4	Round	0.9	11	13.8	390	4.61	956
2	6	Round	0.9	12.1	14.9	470	3.08	1,146
2	10	Round	0.9	13.7	16.7	610	1.83	1,921
2	16	Round	1.25	16.5	19.5	920	1.15	2,193
2	25	Sector-shaped	1.25	18.2	22	1,100	0.727	2,800
2	35	Sector-shaped	1.6	21	24	1,500	0.524	3,624
2	50	Sector-shaped	1.6	24	27	1,850	0.387	8,846
2	70	Sector-shaped	1.6	26	30	2,400	0.268	5,801
2	95	Sector-shaped	2	28	32	3,100	0.193	7,832
2	120	Sector-shaped	2	31	36	3,800	0.153	9,582
2	150	Sector-shaped	2	34	38	4,400	0.124	11,083
2	185	Sector-shaped	2.5	38	43	5,800	0.0991	14,249
2	240	Sector-shaped	2.5	43	48	7,100	0.0754	17,576
2	300	Sector-shaped	2.5	47	53	8,600	0.0601	21,354

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm ²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO ₂ e kg/km]
2	400	Sector-shaped	2.5	52	58	10,500	0.047	26,269
3	1.5	Round	0.9	9.1	11.7	285	12.1	743
3	2.5	Round	0.9	10.4	13.2	360	7.41	904
3	4	Round	0.9	11.6	14.4	440	4.61	1,096
3	6	Round	0.9	12.8	15.6	540	3.08	1,339
3	10	Round	1.25	15.2	18.2	820	1.83	2,033
3	16	Round	1.25	17.4	21	1,100	1.15	2,659
3	25	Round	1.6	23	26	1,700	0.727	4,291
3	35	Round	1.6	25	29	2,100	0.524	5,325
3	50	Sector-shaped	1.6	27	30	2,500	0.387	6,147
3	70	Sector-shaped	1.6	29	33	3,100	0.268	7,790
3	95	Sector-shaped	2	33	37	4,200	0.193	10,553
3	120	Sector-shaped	2	36	40	5,100	0.153	12,816
3	150	Sector-shaped	2.5	41	45	6,400	0.124	16,045
3	185	Sector-shaped	2.5	44	49	7,700	0.0991	19,164
3	240	Sector-shaped	2.5	49	54	9,700	0.0754	24,149
3	300	Sector-shaped	2.5	54	59	11,700	0.0601	29,176
3	400	Sector-shaped	2.5	60	65	14,500	0.047	36,349
4	1.5	Round	0.9	9.8	12.4	315	12.1	835
4	2.5	Round	0.9	11.3	13.9	405	7.41	1,023
4	4	Round	0.9	12.6	15.4	510	4.61	1,275
4	6	Round	1.25	14.7	17.5	730	3.08	1,800
4	10	Round	1.25	16.5	19.5	960	1.83	2,431
4	16	Round	1.25	19.1	23	1,300	1.15	3,173
4	25	Round	1.6	25	28	2,100	0.727	5,214

Copyright Prysmian, all rights reserved. You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this document without written consent of Prysmian. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian. Any modification or alteration of products may cause different results. Prysmian reserves the right to amend the information within this document at any time without notice. For the most up to date information, please contact us. You agree that, in placing any order, you have not relied on the information set out in this document. Prysmian disclaims any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product to the maximum extent permissible by law.

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm ²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO ₂ e kg/km]
4	35	Round	1.6	27	31	2,600	0.524	6,435
4	50	Sector-shaped	1.6	30	34	3,100	0.387	7,622
4	70	Sector-shaped	2	33	37	4,000	0.268	10,212
4	95	Sector-shaped	2	36	41	5,100	0.193	13,030
4	120	Sector-shaped	2.5	41	46	6,600	0.153	16,700
4	150	Sector-shaped	2.5	45	50	7,900	0.124	19,842
4	185	Sector-shaped	2.5	50	55	9,600	0.0991	24,103
4	240	Sector-shaped	2.5	55	61	12,200	0.0754	30,405
4	300	Sector-shaped	2.5	61	66	14,800	0.0601	37,413
4	400	Sector-shaped	3.15	69	75	19,200	0.047	48,186
5	1.5	Round	0.9	11.8	14.6	410	12.1	1,260
5	2.5	Round	0.9	13.3	16.1	500	7.41	1,462
5	4	Round	0.9	14.8	17.8	630	4.61	1,775
5	6	Round	1.25	17.2	21	900	3.08	2,456
5	10	Round	1.25	20	24	1,250	1.83	3,470
5	16	Round	1.6	23	27	1,700	1.15	4,655
5	25	Round	1.6	28	31	2,500	0.727	6,151
5	35	Round	1.6	30	34	2,900	0.524	7,414
7	1.5	Round	0.9	12.8	15.4	475	12.1	1,535
7	2.5	Round	0.9	14.6	17.2	610	7.41	1,829
12	1.5	Round	1.25	16.5	19.5	760	12.1	2,545
12	2.5	Round	1.25	18.9	23	980	7.41	3,026
19	1.5	Round	1.25	18.7	22	960	12.1	3,366
19	2.5	Round	1.6	23	26	1,450	7.41	4,387
27	1.5	Round	1.6	23	27	1,400	12.1	4,773

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm ²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO ₂ e kg/km]
27	2.5	Round	1.6	27	31	1,850	7.41	5,824
37	1.5	Round	1.6	26	29	1,700	12.1	5,930
37	2.5	Round	1.6	30	34	2,300	7.41	7,272

*The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here: <https://uk.prysmiangroup.com/embodied-carbon>