

BS 6724 1kV

LSOH Copper Conductor Armoured Cable. BS 6724. 600/1000 V



Prysmian BS 6724 is a Low Smoke, Zero Halogen (LSOH®) industrial wiring cable for interconnection of systems, control circuitry and power circuits

KEY APPLICATIONS

Designed primarily for clipped directly to a surface, on tray, in basket or in free air. These cables can also be laid direct in ground or in ducts in free draining soil, or embedded in concrete

The design of Prysmian BS 6724 is particularly robust and is well suited to areas at risk of mechanical damage.

FEATURES AND BENEFITS

- Low Smoke, Zero Halogen (LSOH®)
- Manufactured under ISO 9001 Quality management systems
- Single core aluminium wire armour
- Multi core steel wire armour

ADDITIONAL TECHNICAL SUPPORT

- [FAQ's](https://uk.prysmian.com/technical-area/faqs) - uk.prysmian.com/technical-area/faqs
- [Technical email](mailto:tech.info@prysmian.com) - tech.info@prysmian.com
- [Live Chat](https://uk.prysmian.com/technical-area) - uk.prysmian.com/technical-area
- Technical hotline: 02380 295222

STANDARDS



BS 6724

BS EN 60332-1-2

BS EN 60332-3-24

BS EN 61034-2

BS EN 60754-1

Construction Standard

Flame Propagation - Single Cable

Flame Propagation - Multiple (bunched) Cables - Category C

Smoke emission

Corrosive and acid gas

CONSTRUCTION

Conductor material	Copper
Conductor surface	Bare
Core insulation material	XLPE
Armouring/reinforcement	Wire
Armouring	Yes
Material inner sheath	Low smoke zero halogen
Material outer sheath	Low smoke zero halogen
Cable shape	Round

APPLICATIONS PROPERTIES

Nominal voltage U ₀ [V]	600
Nominal voltage U [V]	1,000
Flame retardant	In accordance with BS EN 60332-3-24
Halogen free	Yes
Low smoke	Yes
Max. conductor temperature [°C]	90
Min. Operation temperature [°C]	-25
UV resistant	Yes
Outdoor installation	Yes
Min. Installation temperature [°C]	0
Max. Installation temperature [°C]	80
Underground installation	Yes
Bending radius (rule)	8D

COLOURS

Insulation: Single Core: Brown or Blue;
 Two Cores: Brown, Blue;
 Three Cores: Brown, Black, Grey;
 Four Cores: Blue, Brown, Black, Grey;
 Five Cores: Blue, Brown, Black, Grey, Green/Yellow;
 7 to 37 Cores: White (with printed numbers);
 Sheath: Black

CURRENT RATINGS

Refer to table 4E3 and 4E4 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations

Note: Where a conductor operates at a temperature exceeding 70°C it shall be ascertained that the equipment connected to the conductor is suitable for the conductor operating temperature

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm ²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO ₂ e kg/km]
1	150	Round	1.6	19.6	28	1,900	0.124	6,978
1	185	Round	1.6	22	30	2,300	0.0991	8,206
1	240	Round	1.6	24	32	2,900	0.0754	9,934
1	300	Round	1.6	27	35	3,500	0.0601	11,667
1	400	Round	2	31	40	4,500	0.047	15,219
1	500	Round	2	35	44	5,700	0.0366	17,984
1	630	Round	2	38	48	7,000	0.0283	21,968
1	800	Round	2.5	44	55	9,100	0.0221	29,450
1	1,000	Round	2.5	49	60	11,500	0.0176	36,094
2	1.5	Round	0.9	6.9	10.8	250	12.1	618
2	2.5	Round	0.9	8.2	12.2	315	7.41	737
2	4	Round	0.9	9.2	13.3	375	4.61	874
2	6	Round	0.9	10.4	14.4	450	3.08	1,055
2	10	Round	0.9	11.9	16.2	590	1.83	1,397
2	16	Round	1.25	14	19	890	1.15	2,042
2	25	Sector-shaped	1.25	15.8	22	1,150	0.727	2,661
2	35	Sector-shaped	1.6	17.2	24	1,450	0.524	3,432
2	50	Sector-shaped	1.6	21	28	1,900	0.387	4,453
2	70	Sector-shaped	1.6	23	30	2,400	0.268	5,534
2	95	Sector-shaped	2	25	32	3,100	0.193	7,718
2	120	Sector-shaped	2	28	36	3,700	0.153	9,391
2	150	Sector-shaped	2	30	39	4,500	0.124	11,024
2	185	Sector-shaped	2.5	34	43	5,700	0.0991	13,962
2	240	Sector-shaped	2.5	39	48	7,100	0.0754	17,284
2	300	Sector-shaped	2.5	43	53	8,500	0.0601	20,915

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm ²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO ₂ e kg/km]
2	400	Sector-shaped	2.5	47	58	10,400	0.047	25,771
3	1.5	Round	0.9	7.4	11.2	270	12.1	677
3	2.5	Round	0.9	8.7	12.7	345	7.41	858
3	4	Round	0.9	9.9	13.9	425	4.61	1,005
3	6	Round	0.9	11.1	15.1	520	3.08	1,238
3	10	Round	1.25	12.8	17.7	800	1.83	3,198
3	16	Round	1.25	15	21	1,100	1.15	2,506
3	25	Round	1.6	19.2	26	1,700	0.727	4,096
3	35	Round	1.6	22	28	2,100	0.524	5,082
3	50	Sector-shaped	1.6	24	30	2,500	0.387	5,889
3	70	Sector-shaped	1.6	26	33	3,100	0.268	7,505
3	95	Sector-shaped	2	29	37	4,200	0.193	10,493
3	120	Sector-shaped	2	32	40	5,100	0.153	12,613
3	150	Sector-shaped	2.5	36	45	6,400	0.124	15,794
3	185	Sector-shaped	2.5	40	49	7,700	0.0991	18,948
3	240	Sector-shaped	2.5	45	55	9,700	0.0754	23,875
3	300	Sector-shaped	2.5	49	59	11,700	0.0601	28,790
3	400	Sector-shaped	2.5	55	65	14,400	0.047	35,832
4	1.5	Round	0.9	8.1	11.9	305	12.1	766
4	2.5	Round	0.9	9.6	13.6	395	7.41	952
4	4	Round	0.9	10.9	14.9	495	4.61	1,179
4	6	Round	1.25	12.3	17.2	720	3.08	1,693
4	10	Round	1.25	14.1	19	940	1.83	2,291
4	16	Round	1.25	16.7	22	1,300	1.15	3,006
4	25	Round	1.6	22	28	2,100	0.727	4,979

Copyright Prysmian, all rights reserved. You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this document without written consent of Prysmian. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian. Any modification or alteration of products may cause different results. Prysmian reserves the right to amend the information within this document at any time without notice. For the most up to date information, please contact us. You agree that, in placing any order, you have not relied on the information set out in this document. Prysmian disclaims any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product to the maximum extent permissible by law.

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm ²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO ₂ e kg/km]
4	35	Round	1.6	24	31	2,600	0.524	6,163
4	50	Sector-shaped	1.6	27	34	3,100	0.387	7,332
4	70	Sector-shaped	2	29	37	4,000	0.268	9,991
4	95	Sector-shaped	2	33	41	5,100	0.193	12,786
4	120	Sector-shaped	2.5	37	46	6,600	0.153	16,400
4	150	Sector-shaped	2.5	41	50	7,900	0.124	19,511
4	185	Sector-shaped	2.5	45	55	9,600	0.0991	23,731
4	240	Sector-shaped	2.5	51	61	12,100	0.0754	29,894
4	300	Sector-shaped	2.5	56	66	14,700	0.0601	36,706
4	400	Sector-shaped	3.15	63	75	19,100	0.047	47,463
5	1.5	Round	0.9	10.1	14.8	415	12.1	1,182
5	2.5	Round	0.9	11.5	16.1	500	7.41	1,362
5	4	Round	0.9	13	17.8	630	4.61	1,659
5	6	Round	1.25	14.8	21	900	3.08	2,315
5	10	Round	1.25	17.6	24	1,250	1.83	3,287
5	16	Round	1.6	19.9	27	1,750	1.15	4,439
5	25	Round	1.6	25	32	2,500	0.727	5,882
5	35	Round	1.6	27	34	3,000	0.524	7,140
7	1.5	Round	0.9	11	15.9	495	12.1	1,466
7	2.5	Round	0.9	12.9	17.6	620	7.41	1,738
7	4	Round	1.25	13.7	18.9	830	4.61	2,218
12	1.5	Round	1.25	14.1	21	790	12.1	2,459
12	2.5	Round	1.25	16.5	23	990	7.41	2,887
19	1.5	Round	1.25	16.3	22	960	12.1	3,213
19	2.5	Round	1.6	19.4	26	1,450	7.41	4,203

TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm ²]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO ₂ e kg/km]
19	4	Round	1.6	22	29	1,800	4.61	5,128
27	1.5	Round	1.6	19.7	27	1,450	12.1	4,615
27	2.5	Round	1.6	24	30	1,850	7.41	5,556
37	1.5	Round	1.6	22	29	1,650	12.1	6,375
37	2.5	Round	1.6	27	33	2,300	7.41	9,261

*The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here: <https://uk.prysmiangroup.com/embodied-carbon>