

## FP600s

**Fire Resistant Armoured Power Cable. BS 7846-F120. 600/1000 V**



Prysmian FP600s is the ultimate fire resistant, armoured cable for power of emergency, life safety and fighting systems used in buildings

### KEY APPLICATIONS

Designed primarily for clipped directly to a surface, on tray, in basket or in free air. These cables can also be laid direct in ground or in ducts in free draining soil, or embedded in concrete

Smoke barriers, control dampers, smoke curtains.

Smoke and heat exhaust ventilation systems.

Fire fighting and evacuation lift supplies.

Wet riser pumps.

Extinguishing systems - sprinkler pumps, water mist and powder.

### FEATURES AND BENEFITS

- Fire resistant to BS 7846 F120
- Suitable for use in large and complex buildings to power fire fighting equipment
- BS 8519 Category 1, 2 and 3 for power
- Robust armour provides cable with added mechanical protection
- Reduced flame propagation
- London Underground SI085 Approved Products Register
- Low Smoke, Zero Halogen (LSOH®) sheath
- Manufactured under ISO 9001 Quality management systems
- Designed to meet the requirements of London Underground LUL - SI085
- Multi core steel wire armour

### ADDITIONAL TECHNICAL SUPPORT

- [FAQ's](https://uk.prysmian.com/technical-area/faqs) - [uk.prysmian.com/technical-area/faqs](https://uk.prysmian.com/technical-area/faqs)
- [Technical email](mailto:tech.info@prysmian.com) - [tech.info@prysmian.com](mailto:tech.info@prysmian.com)
- [Live Chat](https://uk.prysmian.com/technical-area) - [uk.prysmian.com/technical-area](https://uk.prysmian.com/technical-area)
- Technical hotline: 02380 295222

### STANDARDS



**BS 7846 - Category F120**

**BS 8491 - 120 Minutes**

**BS 6387 Category CWZ**

**BS EN 60332-1-2**

**BS EN 60332-3-24**

**BS EN 61034-2**

**BS EN 60754-1**

Construction Standard

Fire Resistant Test - Flame, Shock & Water - Up to 120 Minutes

Fire Resistant Tests

Flame Propagation - Single Cable

Flame Propagation - Multiple (bunched) Cables - Category C

Smoke emission

Corrosive and acid gas

## CONSTRUCTION

Conductor material	Copper
Conductor surface	Bare
Core insulation material	Mica + XLPE
Armouring/reinforcement	Wire
Armouring	Yes
Material inner sheath	Low smoke zero halogen
Material outer sheath	Low smoke zero halogen
Cable shape	Round

## APPLICATIONS PROPERTIES

Nominal voltage U <sub>0</sub> [V]	600
Nominal voltage U [V]	1,000
Flame retardant	In accordance with BS EN 60332-3-24
Halogen free	Yes
Low smoke	Yes
Max. conductor temperature [°C]	90
Min. Operation temperature [°C]	-25
UV resistant	Yes
Outdoor installation	Yes
Min. Installation temperature [°C]	0
Max. Installation temperature [°C]	80
Underground installation	Yes
Bending radius (rule)	8D

## COLOURS

Insulation: Two Cores: Brown, Blue;  
 Three Cores: Brown, Black, Grey;  
 Four Cores: Blue, Brown, Black, Grey;  
 Five Cores: Blue, Brown, Black, Grey, Green/Yellow;  
 Sheath: Black

## CURRENT RATINGS

Refer to table 4E4 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations

Note: Where a conductor operates at a temperature exceeding 70°C it shall be ascertained that the equipment connected to the conductor is suitable for the conductor operating temperature

## TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm <sup>2</sup> ]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO <sub>2</sub> e kg/km]
2	4	Round	1.25	15.1	24	1,000	4.61	2,441
2	6	Round	1.25	15.3	23	980	3.08	2,458
2	10	Round	1.25	17.3	23	1,100	1.83	2,617
2	16	Round	1.25	18.5	25	1,250	1.15	2,955
2	25	Round	1.25	21	27	1,550	0.727	3,596
2	35	Round	1.6	24	31	2,100	0.524	4,688
2	50	Sector-shaped	1.6	23	30	2,100	0.387	5,129
2	70	Sector-shaped	1.6	26	33	2,600	0.268	6,347
2	95	Sector-shaped	2	27	36	3,400	0.193	8,685
2	120	Sector-shaped	2	31	39	4,100	0.153	10,418
2	150	Sector-shaped	2	33	42	4,800	0.124	11,989
2	185	Sector-shaped	2.5	37	47	6,100	0.0911	15,119
2	240	Sector-shaped	2.5	41	51	7,500	0.0754	18,378
2	300	Sector-shaped	2.5	45	56	9,000	0.0601	22,068
2	400	Sector-shaped	2.5	50	61	10,900	0.047	26,881
3	4	Round	1.25	15.2	22	950	4.61	2,556
3	6	Round	1.25	15.3	22	920	3.08	2,625
3	10	Round	1.25	18.7	25	1,200	1.83	3,080
3	16	Round	1.25	19.7	26	1,400	1.15	3,503
3	25	Round	1.6	23	30	2,000	0.727	4,730
3	35	Round	1.6	26	33	2,500	0.524	5,609
3	50	Sector-shaped	1.6	26	33	2,700	0.387	6,718
3	70	Sector-shaped	1.6	29	36	3,400	0.268	8,453
3	95	Sector-shaped	2	32	41	4,600	0.193	11,687
3	120	Sector-shaped	2	35	44	5,500	0.153	13,940

## TECHNICAL DATA

Number of cores	Nominal cross section conductor [mm <sup>2</sup> ]	Shape of conductor	Nominal diameter of armouring wire [mm]	Nominal diameter under armour [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO <sub>2</sub> e kg/km]
3	185	Sector-shaped	2.5	43	53	8,200	0.0991	20,489
3	240	Sector-shaped	2.5	47	58	10,300	0.0754	25,531
3	300	Sector-shaped	2.5	52	63	12,300	0.0601	30,600
3	400	Sector-shaped	2.5	58	69	15,100	0.047	37,766
4	4	Round	1.25	16.2	23	960	4.61	2,615
4	6	Round	1.25	15.6	24	1,050	3.08	2,909
4	10	Round	1.25	21	26	1,400	1.83	3,601
4	16	Round	1.25	22	28	1,650	1.15	4,275
4	25	Round	1.6	26	33	2,400	0.727	5,729
4	35	Round	1.6	29	36	3,000	0.524	6,918
4	50	Sector-shaped	1.6	30	37	3,300	0.387	8,373
4	70	Sector-shaped	2	32	41	4,500	0.268	12,293
4	95	Sector-shaped	2	36	45	5,700	0.193	14,679
4	120	Sector-shaped	2.5	40	50	7,300	0.153	18,570
4	150	Sector-shaped	2.5	44	54	8,600	0.124	21,766
4	185	Sector-shaped	2.5	49	59	10,500	0.0991	26,289
4	240	Sector-shaped	2.5	54	65	12,900	0.0754	32,542
4	300	Sector-shaped	2.5	59	70	15,600	0.0601	39,527
4	400	Sector-shaped	3.15	66	79	20,200	0.047	50,443
5	4	Round	1.25	16.8	24	1,050	4.61	2,893
5	6	Round	1.25	18	24	1,150	3.08	3,203
5	10	Round	1.25	23	29	1,650	1.83	4,314
5	16	Round	1.6	25	32	2,100	1.15	5,382
5	25	Round	1.6	28	35	2,800	0.727	6,687
5	35	Round	1.6	32	39	3,300	0.524	7,921

\*The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here: <https://uk.prysmiangroup.com/embodied-carbon>

Copyright Prysmian, all rights reserved. You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this document without written consent of Prysmian. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian. Any modification or alteration of products may cause different results. Prysmian reserves the right to amend the information within this document at any time without notice. For the most up to date information, please contact us. You agree that, in placing any order, you have not relied on the information set out in this document. Prysmian disclaims any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product to the maximum extent permissible by law.