


PRYS201 PVC

PVC Flat Wiring Cable with Insulated CPC. IS 201-4. 300/500 V



EPRYS201

Prysmian PRYS201 PVC is a flat PVC sheathed low voltage wiring cable typically used for small power and lighting applications

KEY APPLICATIONS

Suitable for fixed installation in industrial, commercial and domestic premises, installation in walls, on boards, in conduit, trunking or embedded in plaster for small power and lighting applications

FEATURES AND BENEFITS

- Ideal for ring and radial circuits
- Ideal for lighting and switching circuits
- Easy to strip
- Manufactured under ISO 9001 Quality management systems

ADDITIONAL TECHNICAL SUPPORT

- FAQ's- uk.prysmian.com/technical-area/faqs
- Technical email tech.info@prysmian.com
- Live Chat uk.prysmian.com/technical-area
- Technical hotline: 02380 295222

STANDARDS



BS EN 60332-1-2

Construction Standard

Flame Propagation - Single Cable

CONSTRUCTION

Conductor material Conductor surface Core insulation material Material outer sheath Cable shape Copper Bare

Polyvinyl chloride (PVC) Polyvinyl chloride (PVC)

Flat



APPLICATIONS PROPERTIES

Nominal voltage U0 [V] 300 Nominal voltage U [V] 500

Flame retardant In accordance with BS EN 60332-1-2

Max. conductor temperature [°C] 70
Min. Operation temperature [°C] -15
Min. Installation temperature [°C] 0
Max. Installation temperature [°C] 60

Bending radius (rule) 4D (Minor axis)

COLOURS

Prysmian Cables & Systems Limited, Chickenhall Lane, Eastleigh, Hampshire, SO50 6YU, United Kingdom uk.prysmiangroup.com

Copyright Prysmian Group - 2021

You may not copy, reprint or reproduce in any form the content, either wholly or in part, of this Datasheet, without the written permission of the copyright owner.

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend the information within this Datasheet without prior notice. This Datasheet may include inaccuracies, omissions of content and of information and is not contractually valid unless specifically authorised by Prysmian Group.

CURRENT RATINGS

Refer to IS 10101 National Rules for Electrical Installations. NSAI Standards

SUSTAINABILITY COMMITMENT

At Prysmian, sustainability is at the heart of our mission. By using sustainable processes and materials we are at the forefront of green innovation, promoting resource efficiency in our operations. We also partner with other sustainable companies to advocate responsible practices across our supply chain to reflect our commitment to a greener future. Discover how we are driving the future of sustainable cable and system solutions: <u>Sustainability in the UK | Prysmian</u>.











Scan to find out more

Copyright Prysmian, all rights reserved. You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this document without written consent of Prysmian. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian. Any modification or alteration of products may cause different results. Prysmian reserves the right to amend the information within this document at any time without notice. For the most up to date information, please contact us. You agree that, in placing any order, you have not relied on the information set out in this document. Prysmian disclaims any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product to the maximum extent permissible by law.



 * The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here: https://uk.prysmiangroup.com/embodied-carbon