


## 6181Y 19 Strand

PVC Insulated and Sheathed Single Core Cable. BS 6004. 300/500 V



Prysmian 6181Y (19 strand) is a low voltage single core, PVC insulated copper conductor with an additional PVC oversheath insulation for physical protection

### KEY APPLICATIONS

Fixed installation in dry or damp premises on walls, boards or trays, in channels or embedded in plaster

### FEATURES AND BENEFITS

- 19 strand design offers greater pliability
- Improves reliability and safety in screwed connections
- Comparable weight and dimensions as 7 wire strand
- Easier installation, saves time
- Manufactured under ISO 9001 Quality management systems

### ADDITIONAL TECHNICAL SUPPORT

- [FAQ's](https://uk.prysmian.com/technical-area/faqs) - uk.prysmian.com/technical-area/faqs
- [Technical email](mailto:tech.info@prysmian.com) - tech.info@prysmian.com
- [Live Chat](https://uk.prysmian.com/technical-area) - uk.prysmian.com/technical-area
- Technical hotline: 02380 295222

### STANDARDS



**BS 6004**  
**BS EN 60332-1-2**

Construction Standard  
Flame Propagation - Single Cable

### CONSTRUCTION

Conductor material  
Conductor surface  
Core insulation material  
Material outer sheath  
Cable shape

Copper  
Bare  
Polyvinyl chloride (PVC)  
Polyvinyl chloride (PVC)  
Round

## APPLICATIONS PROPERTIES

Nominal voltage U <sub>0</sub> [V]	300
Nominal voltage U [V]	500
Flame retardant	In accordance with BS EN 60332-1-2
Max. conductor temperature [°C]	70
Min. Operation temperature [°C]	-15
Min. Installation temperature [°C]	0
Max. Installation temperature [°C]	60
Bending radius (rule)	4D

## COLOURS

Insulation: Brown or Blue

Sheath: Brown or Blue

## CURRENT RATINGS

Refer to table 4D1 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations

## TECHNICAL DATA

Nominal cross section conductor [mm <sup>2</sup> ]	Conductor category	Nominal thickness insulation [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO <sub>2</sub> e kg/km]
25	Class 2 = stranded	1.2	10.6	310	0.727	2,004

\*The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here: <https://uk.prysmiangroup.com/embodied-carbon>