


# PROTOTHEN X N2XSY 6/10kV

Distribution and interconnection cable.



Distribution and interconnection cable for industry and power generation networks. Laying: in ground, in tubes, free in air, indoors and in water.

## STANDARDS



<b>IEC 60502-2</b>	General
<b>DIN VDE 0276-620</b>	General
<b>DIN EN 60332-1-2</b>	Fire performance
<b>DIN EN 50575</b>	Fire performance

## CABLE DESIGN

Marketing text 1	Copper: bare, round stranded, class 2
Core insulation material	XLPE
Screen construction	Wire screen and counterhelix tape
Screen	Yes
Screen material	Copper, bare
Material outer sheath	Polyvinyl chloride (PVC)

## ELECTRICAL & THERMAL PARAMETERS

Rated voltage U <sub>0</sub> /U (Um)	6/10 (12) kV
Test voltage [kV]	21
Max. conductor temperature [°C]	90
Max. conductor temperature at short circuit [°C]	250
Min. Installation temperature [°C]	-5

## CHARACTERISTICS

Outdoor installation	Yes
Underground installation	Yes

## CHEMICAL PROPERTIES

Reaction-to-fire class according to EN 13501-6	Fca
--	-----

## ELECTRICAL PROPERTIES

Basic construction	Nominal outer diameter [mm]	Cable weight [kg/km]	Short circuit current conductor (1sec) [kA]	Short circuit current screen (1sec) [kA]
1x35/16	23	880	13.58	3.3
1x35/16	23	880	5.01	3.3
1x50/16	24	1,050	7.15	3.3
1x70/16	26	1,250	10.01	3.3
1x120/16	29	1,800	17.16	3.3
1x150/25	31	2,150	21.45	5.1
1x185/25	32	2,500	26.46	5.1
1x240/25	35	3,050	34.32	5.1
1x300/25	37	3,650	42.9	5.1
1x400/35	40	4,600	57.2	7.1
1x500/35	43	5,600	71.5	7.1

Copyright Prysmian, all rights reserved. You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this document without written consent of Prysmian. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian. Any modification or alteration of products may cause different results. Prysmian reserves the right to amend the information within this document at any time without notice. For the most up to date information, please contact us. You agree that, in placing any order, you have not relied on the information set out in this document. Prysmian disclaims any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product to the maximum extent permissible by law.