
6181Y 19 Strand

PVC Insulated and Sheathed Single Core Cable. BS 6004. 300/500 V



Prysmian 6181Y (19 strand) is a low voltage single core, PVC insulated copper conductor with an additional PVC oversheath insulation for physical protection

KEY APPLICATIONS

Fixed installation in dry or damp premises on walls, boards or trays, in channels or embedded in plaster

FEATURES AND BENEFITS

- 19 strand design offers greater pliability
- Improves reliability and safety in screwed connections
- Comparable weight and dimensions as 7 wire strand
- Easier installation, saves time
- Manufactured under ISO 9001 Quality management systems

ADDITIONAL TECHNICAL SUPPORT

- FAQ's- uk.prysmian.com/technical-area/faqs
- Technical email - tech.info@prysmian.com
- Live Chat - uk.prysmian.com/technical-area
- Technical hotline: 02380 295222

STANDARDS

BS 6004	Construction Standard
BS EN 60332-1-2	Flame Propagation - Single Cable

CONSTRUCTION

Conductor material	Copper
Conductor surface	Bare
Core insulation material	Polyvinyl chloride (PVC)
Material outer sheath	Polyvinyl chloride (PVC)
Cable shape	Round

APPLICATIONS PROPERTIES

Nominal voltage U0 [V]	300
Nominal voltage U [V]	500
Flame retardant	In accordance with BS EN 60332-1-2
Max. conductor temperature [°C]	70
Min. Operation temperature [°C]	-15
Min. Installation temperature [°C]	0
Max. Installation temperature [°C]	60
Bending radius (rule)	4D

COLOURS

Insulation: Brown or Blue

Sheath: Brown or Blue

CURRENT RATINGS

Refer to table 4D1 of BS 7671 Requirements for Electrical Installations. IET Wiring Regulations

Copyright Prysmian, all rights reserved. You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this document without written consent of Prysmian. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian. Any modification or alteration of products may cause different results. Prysmian reserves the right to amend the information within this document at any time without notice. For the most up to date information, please contact us. You agree that, in placing any order, you have not relied on the information set out in this document. Prysmian disclaims any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product to the maximum extent permissible by law.

TECHNICAL DATA

Nominal cross section conductor [mm²]	Conductor category	Nominal thickness insulation [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Conductor resistance at 20° C [Ohm/km]	Embodied Carbon [CO2e kg/km]
25	Class 2 = stranded	1.2	10.6	310	0.727	2,004

*The embodied carbon figure is taken from a single product in the range, for more information on how we calculate our embodied carbon figure visit here:https://uk.prysmiangroup.com/embodied-carbon