

FMSGGO VG95218T63

Halogen-free power cables for marine in acc. with VG 95218 part 63



STANDARDS



VG 95218-63

VG 95218-2

VG 95218-2

General

Fire performance

Chemical behaviour

CABLE DESIGN

Marketing text 1

Copper: plain, round stranded, in accordance with VG 95218 part 63

Core insulation material

Cross-linked LSOH

Screen construction

Braiding

Screen material

Copper, bare

Material outer sheath

Crosslinked polymer

ELECTRICAL & THERMAL PARAMETERS

Nominal voltage DC U [V]	355
Test voltage [kV]	2
Max. operation temperature at conductor [°C]	90
Max. conductor temperature [°C]	90
Max. conductor temperature at short circuit [°C]	250
Min. Installation temperature [°C]	-15
Min. Operation temperature [°C]	-30

CHEMICAL PROPERTIES

Halogen free	acc. BS EN 60754-1/2
Low smoke	acc. BS EN 61034-2
Oil resistant	acc. IEC/EN 60811-404
Ozone resistance	Yes

MECHANICAL PARAMETERS

CABLE PROPERTIES

Basic construction	External code	Diameter conductor [mm]	Cable diameter (min) [mm]	Cable diameter (max) [mm]	Cable weight [kg/km]
2x2x0.75	FMSGSGO 2X2X0,75 (T63)	1.2	11.1	12.5	220
4x2x0.75	FMSGSGO 4X2X0,75 (T63)	1.2	12.9	14.5	330
7x2x0.75	FMSGSGO 7X2X0,75 (T63)	1.2	14.9	16.4	440
11x2x0.75	FMSGSGO 11X0,75 (T63)	1.2	19.6	21.4	710
14x2x0.75	FMSGSGO 14X2X0,75 (T63)	1.2	20.8	22.8	850
19x2x0.75	FMSGSGO 19X2X0,75 (T63)	1.2	23.4	25.4	1,100
24x2x0.75	FMSGSGO 24X2X0,75 (T63)	1.2	26.4	28.4	1,310

CABLE PROPERTIES ELECTRIC

Basic construction	External code	Current carrying capacity [A]	Short circuit current conductor (1sec) [kA]
2x2x0.75	FMSGSGO 2X2X0,75 (T63)	8	0.1
4x2x0.75	FMSGSGO 4X2X0,75 (T63)	6	0.1
7x2x0.75	FMSGSGO 7X2X0,75 (T63)	5	0.1
11x2x0.75	FMSGSGO 11X0,75 (T63)	4	0.1
14x2x0.75	FMSGSGO 14X2X0,75 (T63)	3	0.1
19x2x0.75	FMSGSGO 19X2X0,75 (T63)	3	0.1
24x2x0.75	FMSGSGO 24X2X0,75 (T63)	2	0.1

Copyright Prysmian, all rights reserved. You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this document without written consent of Prysmian. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian. Any modification or alteration of products may cause different results. Prysmian reserves the right to amend the information within this document at any time without notice. For the most up to date information, please contact us. You agree that, in placing any order, you have not relied on the information set out in this document. Prysmian disclaims any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product to the maximum extent permissible by law.