

SPECIALTY CABLE SPEAKER WIRE

Carolprene jacketed cables used for audio and video



PRODUCT CONSTRUCTION:

Conductor: 24 thru 12 AWG fully annealed one bare, one tin stranded copper per ASTM B174

Insulation/Jacket: Premium-grade PVC

Applications: Digital audio · Hi-fi and stereo speaker wire · Jukeboxes · Not for in-wall use · Home theater

Compliances: UL Wires Misc. · RoHS Compliant Directive 2015/863/EU (RoHS-3)

APPLICATION PROPERTIES

Flame retardant	No	Resistant to UV	No
Halogen free	No	Outdoor installation	No
Low smoke	No	Underground installation	No
Oil resistant	No		

STANDARDS AND APPROVALS



We reserve the right to do changes as a result of running product development and/or changes in standards

ELECTRICAL PROPERTIES

Catalog Number	No. Of. Cond	AWG / Kcmil	Conductor category	Conductor strand count	Insulation thickness [in]	Insulation thickness [mm]	Jacket thickness [in]	Jacket thickness [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
C1363	2	12	Class 2 = stranded	65/30	0.025	0.64	0.05	32.07	0.05	32
C1361	2	14	Class 2 = stranded	41/30	0.025	0.64	0.03	18.1	0.03	18.1
C1358	2	16	Class 2 = stranded	26/30	0.02	0.51	0.03	14.24	0.02	14.2
C1357	2	18	Class 2 = stranded	16/30	0.02	0.51	0.02	9.71	0.02	9.71
C1357	2	18	Class 2 = stranded	16/30	0.02	0.51	0.02	9.71	9.71	0.02
C7102A	2	18	Class 2 = stranded	7/0152	0.02	0.51	0.18	4.37	0.172	4.37
C1360	2	20	Class 2 = stranded	10/30	0.02	0.51	0.02	8.77	0.01	8.77
C1362	2	22	Class 2 = stranded	7/30	0.02	0.51	0.02	6.52	0.01	6.51
C1356	2	24	Class 2 = stranded		0.016	0.41	0.02	4.11	0.01	4.1
C1356	2	24	Class 2 = stranded	7/32	0.016	0.41	0.02	4.11	0.01	4.1

We reserve the right to do changes as a result of running product development and/or changes in standards