

## HOOK UP WIRE RUBBER/PVC/POLYETHYLENE

PVC Hook Up wires available in a variety of put ups.



### PRODUCT CONSTRUCTION:

**Conductor:** 20, 18 and 14 AWG fully annealed stranded tinned copper per ASTM B33

**Insulation:** Premium-grade, color-coded rubber, PVC or polyethylene • Temperature range: -40° C to +90° C rubber - 30° C to +105° C PVC -60° C to +80° C polyethylene

**Applications:** Test equipment

**Compliances:** RoHS Compliant Directive 2015/863/EU (RoHS-3)

### APPLICATION PROPERTIES

Flame retardant	No	Resistant to UV	No
Halogen free	No	Outdoor installation	No
Low smoke	No	Underground installation	No
Oil resistant	No		

### STANDARDS AND APPROVALS



We reserve the right to do changes as a result of running product development and/or changes in standards

## ELECTRICAL PROPERTIES

Catalog Number	No. Of. Cond	AWG / Kcmil	Conductor category	Conductor strand count	Insulation thickness [in]	Insulation thickness [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
C1318	1	18	Class 2 = stranded	65/36	0.088	2.24	0.23	5.84
C1321	1	18	Class 2 = stranded	65/36	0.045	1.14	0.15	3.68
C1319	1	20	Class 2 = stranded	41/36	0.047	1.19	0.14	3.56
C1326	1	20	Class 2 = stranded	41/36	0.04	1.02	0.13	3.18

We reserve the right to do changes as a result of running product development and/or changes in standards