

## COMM CABLE MULTI-PAIRED UNSHIELDED CM

UL, CSA, NEC approved wires for two way circuits.



### PRODUCT CONSTRUCTION:

**Conductor:** fully annealed stranded tinned copper per ASTM B33

**Insulation:** Premium-grade, color-coded PVC · Color code: See charts below

**Jacket:** PVC, gray · Temperature range: -20°C to +105°C · Includes ripcord

**Applications:** Public address systems · Intercoms · Internal telephones · Suggested voltage rating: 300 or 600 volts

**Packaging:** Please contact Customer Service for packaging and color options

### APPLICATION PROPERTIES

Flame retardant	No	Resistant to UV	No
Halogen free	No	Outdoor installation	No
Low smoke	No	Underground installation	No
Oil resistant	No		

### STANDARDS AND APPROVALS



CSA Type AWM (105° C, 600 V) NEC/CEC Type CMG (CSA: 105° C, 300 V)

Passes CSA FT4 vertical flame test

We reserve the right to do changes as a result of running product development and/or changes in standards

## ELECTRICAL PROPERTIES

Catalog Number	No. Of. Cond	AWG / Kcmil	Conductor category	Conductor strand count	Insulation thickness [in]	Insulation thickness [mm]	Jacket thickness [in]	Jacket thickness [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
C6360A	12	20	Class 2 = stranded	7/28	0.016	0.41	0.032	0.81	0.354	9
C6702A	4	22	Class 2 = stranded	7/30	0.011	0.28	0.016	0.41	0.155	3.94

We reserve the right to do changes as a result of running product development and/or changes in standards