

FIRE ALARM MULTI CONDUCTOR UNSHIELDED RISER

Copper conductors with premium grade PVC used for Fire alarm systems.



PRODUCT CONSTRUCTION:

Conductors: Stranded or solid bare copper per ASTM B3, B8 and B286 Insulation: Premium-grade, color-coded PVC (See chart below) Jacket: Premium-grade PVC, gray; Sequential footage markings to facilitate installation; Temperature range: -20°C to +75°C Applications: Power-limited control circuits; Wiring of the following systems: Intercom, Security, Audio, Background music; Suggested voltage rating: 300 volts

Nominal Outer Diameter : 2.67 x 5.33 mm. & 0.105 x 0.210 in.

Compliances: NEC Article 725 Type CL3P (UL: 75°C, 150 V) NEC Article 800 Type CMP (UL: 75°C, 300 V) NEC Article 760 Type FPLP (UL: 75°C, 300 V) Suitable for use in the State of California Packaging: Please contact Customer Service for packaging and color options

APPLICATION PROPERTIES

Flame retardant	No	Resistant to UV	No
Halogen free	No	Outdoor installation	No
Low smoke	No	Underground installation	No
Oil resistant	No		

STANDARDS AND APPROVALS



We reserve the right to do changes as a result of running product development and/or changes in standards

ELECTRICAL PROPERTIES

Catalog Number	No. Of. Cond	AWG / Kcmil	Conductor category	Conductor strand count	Insulation thickness [in]	Insulation thickness [mm]	Jacket thickness [in]	Jacket thickness [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
E2542S	2	12	Class 1 = solid	Solid	0.013	0.33	0.015	0.38	0.252	6.4
E1532S	2	12	Class 1 = solid	Solid	0.013	0.33	0.015	0.38	0.244	6.2
E1062S	2	12	Class 2 = stranded	19/0185	0.013	0.33	0.015	0.38	0.26	6.6
E1534S	4	12	Class 1 = solid	Solid	0.013	0.33	0.015	0.38	0.288	7.32
E1054S	2	14	Class 2 = stranded	19/0148	0.013	0.33	0.015	0.38	0.264	6.71
E1052S	2	14	Class 2 = stranded	19/0147	0.013	0.33	0.015	0.38	0.224	5.69
E1522S	2	14	Class 1 = solid	Solid	0.013	0.33	0.015	0.38	0.21	5.33
E2532S	2	14	Class 1 = solid	Solid	0.013	0.33	0.015	0.38	0.218	5.54
E2534S	4	14	Class 1 = solid	Solid	0.013	0.33	0.015	0.38	0.253	6.43
E1524S	4	14	Class 1 = solid	Solid	0.013	0.33	0.015	0.38	0.248	6.29
E1042S	2	16	Class 2 = stranded	19/0117	0.009	0.25	0.015	0.38	0.178	4.52
E2522S	2	16	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.18	4.57
E1512S	2	16	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.172	4.37
E1044S	4	16	Class 2 = stranded	19/0117	0.009	0.25	0.015	0.38	0.21	5.33
E1514S	4	16	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.202	5.13
E2524S	4	16	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.21	5.33
E2502S	2	18	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.158	4.01
E1030S	2	18	Class 1 = solid	Solid	0.008	0.2	0.015	0.38	0.144	3.66
E1032S	2	18	Class 2 = stranded	7/26	0.008	0.2	0.015	0.38	0.154	3.91
E1502S	2	18	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.15	3.81
E1033S	3	18	Class 2 = stranded	7/26	0.008	0.2	0.015	0.38	0.163	4.14

We reserve the right to do changes as a result of running product development and/or changes in standards

ELECTRICAL PROPERTIES

Catalog Number	No. Of. Cond	AWG / Kcmil	Conductor category	Conductor strand count	Insulation thickness [in]	Insulation thickness [mm]	Jacket thickness [in]	Jacket thickness [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
E1034S	4	18	Class 2 = stranded	7/26	0.008	0.2	0.015	0.38	0.18	4.57
E2504S	4	18	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.183	4.65
E1504S	4	18	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.175	4.45
E1036S	6	18	Class 2 = stranded	7/26	0.008	0.2	0.015	0.38	0.216	5.49
E1506S	6	18	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.21	5.33
E2506S	6	18	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.216	5.49
E1038S	8	18	Class 2 = stranded	7/26	0.008	0.2	0.015	0.38	0.245	6.22
E1508S	8	18	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.23	5.84
E2508S	8	18	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.235	5.97
E1040S	10	18	Class 2 = stranded	7/26	0.008	0.2	0.015	0.38	0.282	7.16
E1041S	12	18	Class 2 = stranded	7/26	0.009	0.23	0.015	0.38	0.291	7.39
E1022S	2	20	Class 2 = stranded	7/28	0.007	0.18	0.008	0.2	0.134	3.4
E1024S	4	20	Class 2 = stranded	7/28	0.008	0.2	0.015	0.2	0.156	3.96
E1002S	2	22	Class 2 = stranded	7/30	0.008	0.2	0.015	0.38	0.122	3.1
E1000S	2	22	Class 1 = solid	Solid	0.007	0.2	0.015	0.38	0.118	3
E1003S	3	22	Class 2 = stranded	7/30	0.008	0.2	0.015	0.38	0.13	3.58
E1484S	4	22	Class 1 = solid	Solid	0.01	0.25	0.015	0.38	0.14	3.56
E1001S	4	22	Class 1 = solid	Solid	0.007	0.2	0.015	0.38	0.126	3.2
E1004S	4	22	Class 2 = stranded	7/30	0.008	0.2	0.015	0.38	0.141	3.66
E1006S	6	22	Class 2 = stranded	7/30	0.008	0.2	0.015	0.38	0.164	4.17
E1008S	8	22	Class 2 = stranded	7/30	0.008	0.2	0.015	0.38	0.18	4.57

We reserve the right to do changes as a result of running product development and/or changes in standards

ELECTRICAL PROPERTIES

Catalog Number	No. Of. Cond	AWG / Kcmil	Conductor category	Conductor strand count	Insulation thickness [in]	Insulation thickness [mm]	Jacket thickness [in]	Jacket thickness [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
E1012S	12	22	Class 2 = stranded	7/30	0.008	0.2	0.015	0.38	0.219	5.56

We reserve the right to do changes as a result of running product development and/or changes in standards