

## COMMUNICATION CABLE MULTI CONDUCTOR SHIELDED

UL, CSA, NEC approved wires for two way circuits.



### PRODUCT CONSTRUCTION:

**Conductor:** 20 AWG fully annealed stranded tinned copper per ASTM B33

**Insulation:** Premium-grade, color-coded rubber · Color code: See chart below

**Shield:** 80% tinned copper braid

**Jacket:** Rubber, black · Temperature range: -20°C to +60°C

**Applications:** Control circuits · Broadcast and studio applications · Audio interconnects · Suggested voltage rating: 300 volts

**Features:** Impact- and abrasion-resistant · Stranded conductors for superior flexibility

**Compliances:** RoHS Compliant Directive 2015/863/EU (RoHS-3)

**Packaging:** Please contact Customer Service for packaging and color options

### APPLICATION PROPERTIES

Flame retardant	No	Resistant to UV	No
Halogen free	No	Outdoor installation	No
Low smoke	No	Underground installation	No
Oil resistant	No		

### STANDARDS AND APPROVALS



We reserve the right to do changes as a result of running product development and/or changes in standards

## ELECTRICAL PROPERTIES

Catalog Number	No. Of. Cond	AWG / Kcmil	Conductor category	Conductor strand count	Insulation thickness [in]	Insulation thickness [mm]	Jacket thickness [in]	Jacket thickness [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
C1302	2	20	Class 2 = stranded	26/34	0.02	0.51	0.035	0.89	0.27	6.86
C1304	3	20	Class 2 = stranded	26/34	0.02	0.51	0.035	0.89	0.285	7.24
C1305	4	20	Class 2 = stranded	26/34	0.02	0.51	0.035	0.89	0.3	7.62
C1310	6	20	Class 2 = stranded	26/34	0.02	0.51	0.035	0.89	0.34	8.64

We reserve the right to do changes as a result of running product development and/or changes in standards