

PROTOLON (SM-R)-LWL AWG (N)TSKCGEWOEU 15KV

Portable Power Reeling Cable



Portable Power Reeling Cable, EP Insulation, Semiconductive EP Shield, Neoprene Jacket with reinforcement, Jacket Thickness to ICEA, 90°C

Flexible H.V. reeling cable for extreme mechanical stresses, e.g. high travel speeds.

- Stacker/Reclaimer Reels
- Container Crane Reels
- Log handling Crane Reels
- Ship-unloader Reels
- Ship-loader Reels

CABLE DESIGN

Conductor	Very finely stranded copper, tinned (class FS) PE: Very finely stranded copper, tinned (class FS)
Inner semi-conducting layer	Yes
-	Semi-conductive EPR
Core insulation material	EPR rubber
-	PROTOLON
-	Special compound > 3GI3
Outer semi-conducting layer	Yes
-	Semi-conductive NBR easy-strip
Core arrangement	Three power cores layed up with earth conductor splitted in one or two and additional ground check conductor
Material inner sheath	Rubber - polychloroprene (PCP)
-	Special compound 5GM3
Armouring/reinforcement	Braiding
Armouring/reinforcement material	Polyester
Material outer sheath	Rubber - polychloroprene (PCP)
-	PROTOFIRM
-	Special compound > 5GM5

STANDARDS / APPROVALS



UL file E251483

Based on DIN VDE 0250-813

MSHA P-189-4

DIN VDE 0298-4

DIN EN 60811-404

Reversed bending; roller bending; torsional stress

General

General

Certifications / Approvals

Electrical parameters

Chemical behaviour

Mechanical parameters

ELECTRICAL PARAMETERS

Test voltage [kV]	29
AC test voltage (control cores) [kV]	2
Nominal voltage U [V]	15,000

THERMAL PARAMETERS

Max. conductor temperature [°C]	90
Max. conductor temperature at short circuit [°C]	250
Ambient temperature fix installation (min) [°C]	-40
Ambient temperature fix installation (max) [°C]	80
Ambient temperature flexible installation (min) [°C]	-35
Ambient temperature flexible installation (max) [°C]	60

CHEMICAL PARAMETERS

Flame retardant	In accordance with EN/IEC 60332-1-2
Oil resistant	acc. IEC/EN 60811-404
Ozone resistance	Yes
Resistant to UV	Yes
Sea water resistance	Yes

OPTICAL FIBER PROPERTIES

Fiber type	G62,5/125 µm Multi-mode graded index	G50/125 µm Multi-mode graded index	E9/125 µm Single-mode graded index
Cladding diameter	125 µm	125 µm	125 µm
Fiber diameter	250 µm	250 µm	250 µm
Attenuation at 850 nm	< 3,3 dB/km	< 2,8 dB/km	
Attenuation at 1310 nm	< 0,9 dB/km	< 0,8 dB/km	< 0,4 dB/km
Attenuation at 1550 nm			< 0,3 dB/km
Bandwidth at 850 nm	> 400 MHz	> 400 MHz	
Bandwidth at 1310 nm	> 600 MHz	> 1200 MHz	
Numerical Aperture	0,275 +/- 0,02	0,2 +/- 0,02	0,14 +/- 0,02
Chromatic Dispersion at 1300 nm			< 3,5 ps/nm km
Chromatic Dispersion at 1550 nm			< 18 ps/nm km

MECHANICAL PARAMETERS

Torsional stress +/- [°/m]	25
Permanent tensile strength (rule)	20 N/mm ² static 30 N/mm ² dynamic
Travel speed	- Gantry (reeling operation): no restriction. For speeds beyond 240 m/min it is recommended to consult the cable manufacturer
Bending radius (rule)	Acc. to VDE 0298-3: 6 X D fixed installation 10 X D flexible operation 20 X D min distance with S-type directional changes

CABLE PROPERTIES

Basic construction	SAP code	External code	Diameter conductor [mm]	Cable diameter (min) [mm]	Cable diameter (max) [mm]	Cable weight [kg/km]
3X4AWG+2X8AWG+1XLWL		5DK8***	6.8	57.6	61.6	5,100
3x4AWG+1x5AWG+1x8AWG +1x(12E9LWL)	20412163	5DK8***	6.8	58	62	5,150
3X2AWG+2X6AWG+1X(6G62,5LWL)	20121170	5DK8421	8.4	60.7	64.7	5,820
3X2AWG+1X4AWG+1X8AWG +1X(12G62,5LWL)	20014564	5DK8462	8.4	60.7	64.7	5,870
3X1AWG+2X5AWG+1XLWL		5DK8***	9.5	65.7	69.7	6,800
3x1AWG+1x2AWG+1x8AWG +1x(12E9LWL)	20377643	5DK8***	9.5	65.7	69.7	6,850
3x1/0AWG+2x4AWG+1x(12E9LWL)		5DK8***	10.6	66.9	70.9	7,500
3x1/0AWG+1x1AWG+1x8AWG +1x(12E9LWL)	20377789	5DK8***	10.6	66.9	70.9	7,550
3X2/0AWG+2X3AWG+1XLWL		5DK8***	11.8	70.7	74.7	8,550
3X3/0AWG+2X2AWG+1X(18E9LWL)		5DK8***	13.5	76.8	81	10,240
3X3/0AWG+1X1AWG+1x8AWG +1X(LWL)		5DK8***	13.5	77	81	10,300
3X4/0AWG+2X1AWG+1XLWL		5DK8***	15	80.8	84.8	11,460
3X4/0AWG+2X1/0AWG+1x8AWG +1XLWL		5DK8***	15	80.8	84.8	11,600

CABLE PROPERTIES ELECTRICAL / MECHANICAL

Basic construction	SAP code	External code	Max. tensile strength [N]	Max. tensile strength during acceleration [N]	Current carrying capacity [A]
3X4AWG+2X8AWG+1XLWL		5DK8***	1,270	1,905	132
3x4AWG+1x5AWG+1x8AWG +1x(12E9LWL)	20412163	5DK8***	1,270	1,905	132
3X2AWG+2X6AWG+1X(6G62,5LWL)	20121170	5DK8421	2,020	3,030	176
3X2AWG+1X4AWG+1X8AWG +1X(12G62,5LWL)	20014564	5DK8462	2,020	3,030	176
3X1AWG+2X5AWG+1XLWL		5DK8***	2,540	3,810	204
3x1AWG+1x2AWG+1x8AWG +1x(12E9LWL)	20377643	5DK8***	2,540	3,810	204
3x1/0AWG+2x4AWG+1x(12E9LWL)		5DK8***	3,210	4,815	236
3x1/0AWG+1x1AWG+1x8AWG +1x(12E9LWL)	20377789	5DK8***	3,210	4,815	236
3X2/0AWG+2X3AWG+1XLWL		5DK8***	4,050	6,075	273
3X3/0AWG+2X2AWG+1X(18E9LWL)		5DK8***	5,100	7,650	315
3X3/0AWG+1X1AWG+1x8AWG +1X(LWL)		5DK8***	5,100	7,650	315
3X4/0AWG+2X1AWG+1XLWL		5DK8***	6,430	9,645	364
3X4/0AWG+2X1/0AWG+1x8AWG +1XLWL		5DK8***	6,430	9,645	364



SUSTAINABILITY COMMITMENT

Our commitment to a low-carbon future remains unwavering as we strive to create sustainable solutions while upholding quality standards. We prioritize sustainability and environmental protection in our daily operations, collaborating with local communities to ensure workplace safety and safeguard the areas we operate in.

Sustainability and environmental responsibility is evident also in our **packaging** solutions across the CEE region. We use fully recyclable drum cover foils to minimize environmental impact. Our packaging for rings is made from 30% recycled materials, supporting a circular economy. Additionally, our boxes are made from recyclable, environment-friendly cardboard, promoting eco-conscious choices. By choosing Prysmian, you are not only selecting high-quality products but also contributing to a greener future.

Check for more details about our sustainability commitment here: [Sustainability report and responsibility](#).

Current carrying capacity acc. VDE 0298-4, installed free in air at 30°C ambient temperature