

LAMP CORD

Specialty Cord that carries the latest listings/certifications



PRODUCT CONSTRUCTION:

Conductor: 18 and 16 AWG fully annealed bare or tinned copper

Insulation: Premium-grade, color-coded PVC · Temperature range: -20°C to +60°C

Jacket Marking: Print type: Indent print · (SIZE) SPT-1 E11368 60°C (UL)--CSA LL9993 FT2 --- 300 VOLT ROHS ORIGIN USA

Applications: Small appliances · Lamps · Radios · Jukeboxes

Industry Approvals: UL Listed · CSA Certified · RoHS Compliant

Nominal Outer Diameter : 0.107 X 0.21 in. & 2.72 X 5.33 mm.

STANDARDS AND APPROVALS



APPLICATION PROPERTIES

Flame retardant	No	Resistant to UV	Yes
Halogen free	No	Outdoor installation	Yes
Low smoke	No	Underground installation	No
Oil resistant	No		

We reserve the right to do changes as a result of running product development and/or changes in standards

ELECTRICAL PROPERTIES

Catalog Number	No. Of. Cond	AWG / Kcmil	Conductor strand count	Insulation thickness [in]	Insulation thickness [mm]	Nominal overall o.d.	Nominal outer diameter [mm]	Ampacity	Cable weight [lbs/ft]	Colour outer sheath
02303	2	16	65/34	0.045	1.14	0.046	29.51	13	37	White
02303	2	16	65/34	0.045	1.14	0.046	29.51	13	37	Brown
02303	2	16	65/34	0.045	1.14	0.046	29.51	13	37	Black
02301	2	18	41/34	0.03	0.76	0.022	14.5	10	22	Black
02301	2	18	41/34	0.03	0.76	0.022	14.5	10	22	White
02301	2	18	41/34	0.03	0.76	0.022	14.5	10	22	Brown
02304	2	18	41/34	0.03	0.76	0.022	14.5	10	22	Other
02306	2	18	41/34	0.03	0.76	0.022	14.5	10	22	Other
02301	2	18	41/34	0.03	0.76	0.022	14.5	10	22	Other

We reserve the right to do changes as a result of running product development and/or changes in standards