

RG 174/U Type

Coaxial Cable



PRODUCT CONSTRUCTION:

- Conductors:** Copper-clad steel per ASTM B869
- Insulation/Core:** Solid polyethylene (PE)
- Shield:** Tinned copper braid
- Jacket:** Premium PVC compound
- Applications:** Suitable for RF signal transmission
- Shield Coverage NOM SHLD DCR:** 88% Tinned Copper Braid 10.3 Ω/Mft.
- Nominal Capacitance:** 30.00 pF/ft - 98.43 pF/m
- Velocity of Propagation:** 66%
- Nominal Impedance:** 50 Ω

APPLICATION PROPERTIES

Flame retardant	No	Outdoor installation	No
Halogen free	No	Underground installation	No
Resistant to UV	No		

STANDARDS AND APPROVALS



ELECTRICAL PROPERTIES

Catalog Number	AWG / Kcmil	Nom. insulation o.d. [in]	Nominal diameter over insulation [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
C1156	26	0.059	1.5	0.103	2.62

We reserve the right to do changes as a result of running product development and/or changes in standards