

RG 174/U Type

Coaxial Cable



PRODUCT CONSTRUCTION:

Conductors: Copper-clad steel per ASTM B869

Insulation/Core: Solid polyethylene (PE)

Shield: Tinned copper braid

Jacket: Premium PVC compound

Applications: Suitable for RF signal transmission

Shield Coverage NOM SHLD DCR: 88% Tinned Copper Braid 10.3 Ω /Mft.

Nominal Capacitance: 30.00 pF/ft - 98.43 pF/m

Velocity of Propagation: 66%

Nominal Impedance: 50 Ω

APPLICATION PROPERTIES

Flame retardant	No	Outdoor installation	No
Halogen free	No	Underground installation	No
Resistant to UV	No		

STANDARDS AND APPROVALS



ELECTRICAL PROPERTIES

Catalog Number	AWG / Kcmil	Nom. insulation o.d. [in]	Nominal diameter over insulation [mm]	Nominal overall o.d.	Nominal outer diameter [mm]
C1156	26	0.059	1.5	0.103	2.62

We reserve the right to do changes as a result of running product development and/or changes in standards